

Frequency Standards Component Oscillators Series 9400

Introduction

Racal-Dana crystal controlled frequency standards feature low power consumption, good temperature stabilization, and excellent aging performance. This makes them ideal for use in communications equipment and precision instruments. They are built to stringent

military specifications and use high quality glass or coldweld sealed crystals. During production, the temperature and aging performance of each oscillator is checked and recorded. Small size, rugged construction, and fast warm-up characteristics make these oscillators particularly suitable for transportable equipment.

Specifications

Model Number	9420	9421	9442/5, 12	9443
Output Frequency	5 MHz			
Output Level (Peak-to-Peak)	1V into 50 ohms		1V into 1000 ohms	
Operating Temperature	-10°C to +60°C			
Daily Aging Rate (after 3 months)	$< 5 \times 10^{-10}$		$< 3 \times 10^{-9}$	
Warm-up Time	20 minutes to 1×10^{-7}		6 minutes to 2×10^{-7}	
Stability with Temperature Change (per °C)	$\pm 6 \times 10^{-10}$		$\pm 3 \times 10^{-9}$	$\pm 4 \times 10^{-9}$
Stability with 10% Supply Voltage Change	$\pm 5 \times 10^{-9}$	$\pm 3 \times 10^{-9}$	$\pm 4 \times 10^{-9}$	
Stability with 10% Load Change	$\pm 5 \times 10^{-9}$	$\pm 3 \times 10^{-9}$	$\pm 5 \times 10^{-9}$	
Trim Range (parts in 10^7)	-8 to +2	-7 to +3	-60 to +30	
Supply Voltage	12V	5V	5V or 12V	5V
Typical Supply Current (after Warm-up)	120 mA	250 mA	150 mA (5V) 60 mA (12V)	170 mA
Dimensions	51 x 51 x 96 mm (2 x 2 x 3.75 inches)		51 x 51 x 51 mm (2 x 2 x 2 inches)	51 x 51 x 32 mm (2 x 2 x 1.25 inches)
Base	B7G			

Series 9400 Ordering Information

Model 9420: Oven Reference Oscillator

Model 9421: Oven Reference Oscillator

Model 9442/5: Fast Warm-Up Oven Oscillator

Model 9442/12: Fast Warm-Up Oven Oscillator

Model 9443: Miniature Fast Warm-Up Oven Oscillator